


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	LENGTH (MIN)
P110PC2IG1MJY	1M
P110PC2IG2MJY	2M
P110PC2IG3MJY	3M
P110PC2IG5MJY	5M

IDENTIFICATION LABEL

SHIELDED MODULAR PLUG

PLUG POSITION 1

110 CONTACT 1

PLUG POSITION: CABLE WIRE:

1	WHITE/BLUE
2	BLUE
3	WHITE/ORANGE
4	VACANT
5	VACANT
6	ORANGE
7	VACANT
8	VACANT

110 CONTACT: CABLE WIRE:

1	WHITE/BLUE
2	BLUE
3	WHITE/ORANGE
4	ORANGE

- NOTES:
1. TERMINATED WITH (8 POSITION) MODULAR PLUG AND A 110 CONNECTOR.
  2. THE PATCH CORD CAN BE USED WITH PAN-PUNCH™ 110 CONNECTING BLOCKS.
  3. CONSTRUCTED WITH 2 PR/24AWG STRANDED TWISTED CAT5 UTP NON-PLENUM PATCH CABLE WITH 24AWG STRANDED TINNED COPPER CONDUCTORS.  
CABLE COLOR: GRAY
  4. MATERIAL:  
110 CONNECTOR: POLYCARBONATE  
PLUG: POLYCARBONATE
  5. 110 CONNECTOR FEATURES INCLUDE A CLEAR CAP TO ENSURE PROPER WIRE SEQUENCE AND CONNECTOR ORIENTATION. RETAINING CLIPS SECURE THE JACKET CLOSE TO THE POINT OF TERMINATION WHICH MINIMIZES WIRE UNTWISTING. INTEGRAL STRAIN RELIEF MINIMIZES STRESS ON WIRES DURING DISCONNECTION.
  6. POLARIZED TO PREVENT REVERSE INSTALLATION TO CONNECTOR BLOCK.

PART NUMBER		P110PC2IG*MJY	
TITLE			
110 TO RJ45 TWO PAIR PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		M00242CE/00	
DATASET FILE NAME		M00242CE_DC29/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 (.3)		SEE NOTE 4	
.xx ± .03 (.8) ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		00242-29	
DRAWN BY	DATE	CHK	SCALE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5-28-14	MDJR	REFR	EJH	A. UPDATED TITLE BLOCK.	00242-29
R	5-01-07	BJN	EJH	EJH	RELEASED TO PRODUCTION	00242-29

D10100DA/14