


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

2

1



CONTACT	WIRE COLOR
1	WHITE/BLUE
2	BLUE
3	WHITE/ORANGE
4	ORANGE
5	WHITE/GREEN
6	GREEN
7	WHITE/BROWN
8	BROWN

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
- 110 CONNECTORS ON BOTH ENDS. THE PATCH CORDS CAN BE USED WITH PAN-PUNCH™ 110 CONNECTING BLOCKS.
- FEATURES INCLUDE A CLEAR CAP TO ENSURE PROPER WIRE SEQUENCE AND CONNECTOR ORIENTATION. RETAINING CLIPS SECURE THE JACKET CLOSE TO THE POINT OF TERMINATION WHICH MINIMIZES WIRE UNTWISTING. INTEGRAL STRAIN RELIEF MINIMIZES STRESS ON WIRES DURING DISCONNECTION.
- POLARIZED TO PREVENT REVERSE INSTALLATION TO CONNECTOR BLOCK.
- CATEGORY 5e UNSHIELDED TWISTED PAIR CABLE WITH 24AWG STRANDED TINNED COPPER CONDUCTORS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANDUIT P/N	MIN. CABLE LENGTH	WEIGHT
P110PC41G2Y	2 FT.	.83 LB/ 10 PCS (376.5 g/ 10PCS)
P110PC41G3Y	3 FT.	1.05 LB/ 10 PCS (476.3 g/ 10PCS)
P110PC41G4Y	4 FT.	1.25 LB/ 10 PCS (566.9 g/ 10PCS)
P110PC41G5Y	5 FT.	1.46 LB/ 10 PCS (662.2 g/ 10PCS)
P110PC41G6Y	6 FT.	1.67 LB/ 10 PCS (757.5 g/ 10PCS)
P110PC41G7Y	7 FT.	1.88 LB/ 10 PCS (852.8 g/ 10PCS)
P110PC41G8Y	8 FT.	2.09 LB/ 10 PCS (948.0 g/ 10PCS)
P110PC41G9Y	9 FT.	2.30 LB/ 10 PCS (1043.3g/ 10PCS)
P110PC41G12Y	12 FT.	2.93 LB/ 10 PCS (1329.0g/ 10PCS)
P110PC41G15Y	15 FT.	3.56 LB/ 10 PCS (1614.8g/ 10PCS)
P110PC41G18Y	18 FT.	4.19 LB/ 10 PCS (1900.8g/ 10PCS)
P110PC41G.5MY	.5M	.75 LB/ 10 PCS (342.0 g/ 10PCS)
P110PC41G1MY	1M	1.09 LB/ 10 PCS (494.4 g/ 10PCS)
P110PC41G1.5MY	1.5M	1.44 LB/ 10 PCS (653.2 g/ 10PCS)
P110PC41G2MY	2M	1.78 LB/ 10 PCS (807.4 g/ 10PCS)
P110PC41G3MY	3M	2.48 LB/ 10 PCS (1120.4g/ 10PCS)
P110PC41G5MY	5M	3.85 LB/ 10 PCS (1748.1g/ 10PCS)

PART NUMBER		P110PC4IG*Y, P110PC4IG*MY	
TITLE			
CATEGORY 5e 110 PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479JS/00	
DATASET FILE NAME		M02479JS_DC255/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xx ± .03 [.8]		.xxx ± .010 [ .3 ]	
ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-255	
DRAWN BY	DATE	CHK	SCALE
NER	3-17-06	WJC	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/28/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-255
R	3-17-06	NER	WJC	RMD	RELEASED TO PRODUCTION	02479-255

2

1

D10100DA/14